

Four-sided /Eight-sided Applicator

A flexible and easy to use applicator, combining 4 gaps or 8 gaps size in one unit. The cylindrical shape provides excellent results particularly on firm substrates and smooth surface. By simply rotation through 90 angles, the next gap size is placed onto the test surface. It is designed with ASTM D 823-25 and made of high-grade, corrosion-resistant stainless steel 440C.

Main Technical Parameters:

- ★ Wet Film Width of: BGD 205→160mm; BGD 206/207→80mm;
- ★ The total length: BGD 205→190mm; BGD 206/207→100mm;

★ Ordering Information:

Universal Type


- BGD 206/1: (5μm, 10μm, 15μm, 20μm)
- BGD 206/2: (25μm, 50μm, 75μm, 100μm)
- BGD 206/3: (50μm, 100μm, 150μm, 200μm)
- BGD 206/4: (30μm, 60μm, 90μm, 120μm)
- BGD 206/5: (100μm, 200μm, 300μm, 400μm)
- BGD 206/6: (50μm, 75μm, 100μm, 150μm)
- BGD 206/7: (100μm, 150μm, 200μm, 250μm)
- BGD 206/8: (250μm, 500μm, 750μm, 1000μm)

Long Type


- BGD 205/2: (25μm, 50μm, 75μm, 100μm)
- BGD 205/3: (50μm, 100μm, 150μm, 200μm)
- BGD 205/4: (30μm, 60μm, 90μm, 120μm)
- BGD 205/5: (100μm, 200μm, 300μm, 400μm)
- BGD 205/6: (50μm, 75μm, 100μm, 150μm)
- BGD 205/7: (100μm, 150μm, 200μm, 250μm)
- BGD 205/8: (250μm, 500μm, 750μm, 1000μm)

Eight-sided Type


- BGD 207/2: (25μm, 50μm, 75μm, 100μm, 150μm, 200μm, 300μm, 400μm)



BGD 206



BGD 205



BGD 207/2

Biuged accepts any order for customized special applicators!